## **Specifications**

For other materials or modifications, please consult TESCOM.

#### **OPERATING PARAMETERS**

Pressure rating per criteria of ANSI/ASME B31.3

#### **Maximum Inlet Pressure**

15,000 psig / 1034 bar

#### **Controlled Pressure Ranges**

0-500, 0-800, 10-1500, 15-2500, 25-4000, 50-6000, 200-10,000, 300-15,000 psig

0-34.5, 0-55.2, 0.69-103, 1.0-172, 1.7-276, 3.4-414, 13.8-690, 20.7-1034 bar

#### **Design Proof Pressure**

150% maximum rated

#### Leakage

Maximum 2 drops/minute at 150 SUS at 2500 psig / 172 bar

## Ambient Operating Temperature<sup>1</sup>

-15°F to 165°F / -26°C to 74°C

## **Flow Capacity**

 $C_{V} = 0.08$ 

## **Maximum Operating Torque**

40 in-lbs / 4.5 N•m

### MEDIA CONTACT MATERIALS

## **Body**

316 Stainless Steel

#### **Seat and Poppet**

17-4 PH Stainless Steel

#### O-Rina

See Part Number Selector

## **Back-up Ring**

## **Inlet Pressure Ranges**

2500-10,000 psig / 172-690 bar: PTFE 15,000 psig / 1034 bar: PCTFE

## Valve Seal

Polyimide (Vespel®)

#### Sensor Seal

#### **Inlet Pressure Ranges**

500-10,000 psiq / 34.5-690 bar: PCTFE 15,000 psiq / 1034 bar: Polyimide (Vespel®)

#### **Remaining Parts**

300 Series Stainless Steel

## **OTHER**

## Cleaning

CGA 4.1 and ASTM G93

### Weiaht

5 lbs / 2.3 kg

1. For extended temperatures from -40°F to 400°F / -40°C to 204°C, consult TESCOM. Teflon®, Viton®, Kalrez®, and Vespel® are registered trademarks of E.I. du Pont de Nemours and Company.



TESCOM 54-2100 Series backpressure regulator is suitable for 15,000 psiq / 1034 bar liquid applications. Modifications are also available for 20,000 psig / 1379 bar and 30,000 psiq / 2068 bar. Hardened Stainless Steel seat and stem provide excellent wear resistance in harsh applications.

# **Applications**


- Pump discharge pressure control
- Chemical injection
- Burst testing

### **Features and Benefits**

- Accuracy ± 1% of control pressure range
- Easily adjusted, low torque handknob control, dome and air loaded versions are available
- · Hardened Stainless Steel seats
- Safe and reliable piston-style sensor
- · Panel mounting is standard
- Compatible with TESCOM's air actuator and **ER5000 Electropneumatic Controllers**


## **54-2100 SERIES**

## 54-2100 Series Regulator Drawing



## 54-2100 Series Regulator Flow Chart

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.



FLOW RATE - GPM [LPM] Hydraulic Fluid - Mobil DTE 20 Series

# **54-2100 SERIES**

# 54-2100 Series Regulator Part Number Selector

Repair Kits, Accessories & Modifications may be available for this product. Please contact TESCOM for more information.

Example for selecting a part number:

54-21 6 1 D 2

BASIC SERIES	BODY MATERIAL	INLET PRESSURE	SOFT GOODS MATERIAL			INLET	INLET	
			DYNAMIC	STATIC	SEAT	AND OUTLET PORT TYPE	AND OUTLET PORT SIZE	LOADING
54-21	6 – 316 Stainless Steel	<ul> <li>0 - 300-15,000 psig 20.7-1034 bar¹ (Spring only)</li> <li>1 - 200-10,000 psig 13.8-690 bar²</li> <li>2 - 50-6000 psig 3.4-414 bar (Spring and Air only)</li> <li>3 - 25-4000 psig 1.7-276 bar (Spring only)</li> <li>4 - 15-2500 psig 1.0-172 bar (Spring and Air only)</li> <li>5 - 10-1500 psig 0.69-103 bar (Spring and Air only)</li> <li>6 - 0-800 psig 0-55.2 bar</li> </ul>	D – Nitrile, Buna-N T – FKM (Viton®-A) V – FFKM, Perfluoroelastomer (Kalrez®) Z – Ethylene Propylene	(Kalrez®)	17-4 Stainless Steel 17-4 Stainless Steel 17-4 Stainless Steel 17-4 Stainless Steel	1 – SAE 2 – NPTF 3 – MS33649 4 – High Pressure/ Amico 6 – Medium Pressure/ Slimline	4 – 1/4" 6 – 3/8" 8 – 1/2" (NPTF/SAE/ MS33649 only) 9 – 9/16" (MP/HP only) 12 – 3/4" (MP only)	– Spring (no letter required) <b>H</b> – Dome <b>A</b> – Air <sup>3</sup>
		(Spring only) 7 – 0-500 psig 0-34.5 bar (Spring and Dome only)		d temperatures of so ease consult TESCOI	oft goods 2	. Available with 1/4" and 3/ 3/8" medium pressure, 1/ . Not to be used with 3/8" S . 80 psig / 5.5 bar minimur	4" NPTF only AE or 3/8" MS33649 p	orts